



Main

Range of product	Unica
Device application	Mounting
Product or component type	Switched fuse mechanism
Device presentation	Mechanism with fixing frame
Colour tint	Aluminium

Complementary

Pilot light	Neon indicator
Rated current	13 A at 250 V AC, resistive
Network frequency	50 Hz
Number of modules	2 modules
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Tightening torque	0.4 N.m
Terminal identifier	Earth L in N out N in L out
Clamping connection capacity	2 x 4 mm ² input 3 x 2.5 mm ² input 1 x 1.5 mm ² output 1 x 2.5 mm ² output
Cable cross section	4 Mm ² flexible cable 4 Mm ² rigid cable 4 Mm ² stranded cable 2.5 Mm ² rigid cable 2.5 Mm ² stranded cable 2.5 Mm ² flexible cable 1.5 Mm ² rigid cable 1.5 Mm ² stranded cable 1.5 mm ² flexible cable
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Standards	BS 7671 BS 1363-4
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Projecting depth	10 mm
Embedding depth	35 mm
Width	81 mm

Height	83 mm
Net weight	0.076 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	11.7 cm
Package 1 Length	16 cm
Package 1 Weight	76 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	610 g
Unit Type of Package 3	P12
Number of Units in Package 3	1600
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	175000 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations