



## Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

## Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 838 m <sup>3</sup> /h at 50 Hz Free flow rate with standard filter: 803 m <sup>3</sup> /h at 60 Hz
[Us] rated supply voltage	207...244 V
Input voltage	230 V 50/60 Hz

## Complementary

Absorbed power	150 W 50 Hz 195 W 60 Hz
[In] rated current	0.65 A 50 Hz 0.85 A 60 Hz
Noise level < at	75...76 dB
Bearing type	Ball
Height	External: 336 mm
Width	External: 316 mm
Depth	External : 162 mm
Cut-out dimensions	291 x 291 mm
Net weight	4.1 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient air temperature for operation	-15...60 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	170 Pa flow rate 0 m <sup>3</sup> /h
Connections - terminals	Terminal block
IP degree of protection	IP54

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Device composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template
Condition of use	Outside temperature must be 5 °C lower than inside temperature Flow rates depends on the work point, see ProClima software Overfrequent filter replacement should be avoided Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.000 cm
Package 1 Width	32.000 cm
Package 1 Length	34.000 cm
Package 1 Weight	4.386 kg
Unit Type of Package 2	P12
Number of Units in Package 2	24
Package 2 Height	110.000 cm
Package 2 Width	120.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	116.000 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------