

Product data sheet

Characteristics

VX5VPM001

Wear part, fan for variable speed drive, Altivar Process 600 900, floor standing, from 110 to 315kW, from 380 to 440V



Main

Range Compatibility	Altivar Process 600/900
Accessory / separate part type	Fan kit
Accessory / separate part category	Cooling accessory
Product or Component Type	Fan

Complementary

Kit composition	Fan Mounting bracket Instruction sheet
Product compatibility	Variable speed drive ATV630 floor-standing 110 kW 380...440 V Variable speed drive ATV630 floor-standing 132 kW 380...440 V Variable speed drive ATV630 floor-standing 160 kW 380...440 V Variable speed drive ATV630 floor-standing 200 kW 380...440 V Variable speed drive ATV630 floor-standing 250 kW 380...440 V Variable speed drive ATV630 floor-standing 315 kW 380...440 V Variable speed drive ATV650 floor-standing 110 kW 380...440 V Variable speed drive ATV650 floor-standing 132 kW 380...440 V Variable speed drive ATV650 floor-standing 160 kW 380...440 V Variable speed drive ATV650 floor-standing 200 kW 380...440 V Variable speed drive ATV650 floor-standing 250 kW 380...440 V Variable speed drive ATV650 floor-standing 315 kW 380...440 V Variable speed drive ATV930 floor-standing 110 kW 380...440 V Variable speed drive ATV930 floor-standing 132 kW 380...440 V Variable speed drive ATV930 floor-standing 160 kW 380...440 V Variable speed drive ATV930 floor-standing 200 kW 380...440 V Variable speed drive ATV930 floor-standing 250 kW 380...440 V Variable speed drive ATV930 floor-standing 315 kW 380...440 V Variable speed drive ATV950 floor-standing 110 kW 380...440 V Variable speed drive ATV950 floor-standing 132 kW 380...440 V Variable speed drive ATV950 floor-standing 160 kW 380...440 V Variable speed drive ATV950 floor-standing 200 kW 380...440 V Variable speed drive ATV950 floor-standing 250 kW 380...440 V Variable speed drive ATV950 floor-standing 315 kW 380...440 V

Ordering and shipping details

Category	US1CP4E22230
Discount Schedule	CP4E
GTIN	3606485406824
Returnability	Yes
Country of origin	ID

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.94 in (10.0 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	2.95 lb(US) (1.336 kg)
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	11.53 lb(US) (5.23 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes