



Main

Range of product	Altivar
Range compatibility	Easy Altivar 610 Altivar Machine ATV340
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To control, adjust and configure the drive To display the current values To save and download configurations
IP degree of protection	IP21

Complementary

User language	French German English Spanish Italian Chinese
Realtime clock	Without
Display type	Backlit LCD screen white
Messages display capacity	2 lines
Pixel resolution	128 x 64
Net weight	0.05 kg





Environment

Ambient air temperature for operation	-15...50 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.700 cm
Package 1 Width	9.200 cm
Package 1 Length	12.400 cm
Package 1 Weight	99.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	45
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.360 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov