

Main

Range of product	Modicon Transformer Economic
Product or component type	Safety and isolation transformer
Rated power in VA	63 VA
Input voltage	230 V AC phase to phase, terminal(s): L1-L2 230 V AC single phase, terminal(s): N-L1
Output voltage	24 V AC
Secondary winding	Single
Protective cover	Without
Ambient air temperature for operation	-20...40 °C

Complementary

Input voltage limits	207...253 V
Network frequency limits	47...63 Hz
Input voltage tolerance	+/- 15 V
Efficiency	82 %
Power dissipation in W	13.8 W
Voltage variation at nominal load	0,116 at 230 V
Output sustained overvoltage	0,136 (no load, hot state)
Maximum voltage drop at rated load	14.13 %
No load losses	5.7 W
Short-circuit voltage	0,133
Output protection type	Against overload, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection Against overvoltage, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection Against short-circuits, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection
Connections - terminals	For input connection: screw type terminals, connection capacity: 4 x 2.5...4 x 4 mm ² AWG 14...AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 2.5...1 x 4 mm ² AWG 14...AWG 11 For output connection: screw type terminals, connection capacity: 2 x 2.5...2 x 4 mm ² AWG 14...AWG 11
Marking	CE
Fixing mode	By 4 screws diameter: 5 mm on vertical panel, operating position: vertical By 4 screws diameter: 5 mm on horizontal panel with derating to 90 %, operating position: horizontal By clips (with mounting plate) on 35 mm symmetrical DIN rail By 4 screws diameter: 5 mm on vertical panel
Operating altitude	3000 m
Electrical insulation class	Class B
Width	79.0 mm
Height	70.0 mm
Depth	91.0 mm
Net weight	1.15 kg

Environment

Product certifications	EAC[RETURN]DNV-GL
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % during operation
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	3200 V between input and ground 3200 V between output and ground 5100 V between input and output

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.200 cm
Package 1 Width	12.500 cm
Package 1 Length	14.800 cm
Package 1 Weight	1.347 kg
Unit Type of Package 2	P06
Number of Units in Package 2	57
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	88.696 kg


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile
PVC free	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
79	91	70	56	48	4.8


Dimensions in in.

a	b	c	G	J	Ø
3.11	3.58	2.76	2.20	1.89	0.19

Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring

