



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Movement detector
Load type	Capacitive: : 6 A, 28 µF, AC Halogen lamp: 1000 W, AC Compact fluorescent lamp: 4 x 23 W, AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 315 VA Fluorescent tube: 250 VA, AC Incandescent lamp: 1000 W, AC
Colour tint	White
Type of packing	Carton

Complementary

[Ue] rated operational voltage	220...240 V
Network frequency	50 Hz
[Ue] rated operational voltage	220...240 V
Output current	10 A
Type of setting	Time adjustment Light sensitivity adjustable
Time delay	3 s...10 min
Light intensity adjustment	5...2000 lux
Horizontal detection angle	0...360 °
Detection range	Radius: 3.9 m
Material	ABS + PC matt
Device mounting	Ceiling
Mounting height	2.4 m

Environment

Condition of use	Indoor use only
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	14.0 cm
Package 1 Length	14.2 cm
Package 1 Weight	316.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.42 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------