



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Movement detector
Load type	Incandescent lamp: 1000 W, AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 315 VA Fluorescent tube: 250 VA, AC Compact fluorescent lamp: 4 x 23 W, AC Capacitive: : 6 A, 28 µF, AC Capacitive: : 10 A, 21 µF, AC Halogen lamp: 800 W, AC
Colour tint	White
Type of packing	Carton

### Complementary

[Ue] rated operational voltage	220...240 V
Network frequency	50 Hz
[Ue] rated operational voltage	220...240 V
Output current	10 A
Type of setting	Time adjustment Light sensitivity adjustable
Time delay	5 s...20 min
Light intensity adjustment	5...2000 lux
Horizontal detection angle	0...360 °
Detection range	Frontal: 12 m
Material	PC (polycarbonate) matt
Device mounting	Surface
Mounting height	2.5 m

### Environment

IP degree of protection	IP55
Ambient air temperature for operation	-15...40 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	17.200 cm
Package 1 Length	10.000 cm
Package 1 Weight	415.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.911 kg

Unit Type of Package 3	P12
Number of Units in Package 3	432
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	187.944 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------