



### Main

Range	Prisma
Range of product	Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma Prisma G duct Prisma Prisma Pack 250 duct
Type of front plate	Cut-out
Installed device	EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P: mounting plate support: CVS100...160 vertical installation 1 x 4P: mounting plate support: CVS100...160 vertical installation 1 x 3P: mounting plate support: CVS250 vertical installation 1 x 4P: mounting plate support: CVS250 vertical installation
Operating position	Vertical

### Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 300 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	9
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	450 mm
Width	300 mm
Net weight	0.98 kg

Quantity per set	Set of 1
Functional unit	300 mm Prisma G floor-standing duct EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9

## Environment

IP degree of protection	IP30
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	980.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	27.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	10.24 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240
Package 3 Height	82.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	257.76 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product