



Main

Range	Prisma
Range of product	Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma Prisma G enclosure
Type of front plate	Cut-out
Installed device	ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: toggle - horizontal installation Human-switchboard interface: 96 x 96 mm device Human-switchboard interface: HSI Enerlin'X: fixed FDM121 - control: remote control - vertical installation
Poles description	1 x 3P: mounting plate support: NSX100...160 horizontal installation 1 x 4P: mounting plate support: NSX100...160 horizontal installation 1 x 3P: mounting plate support: NSX250 horizontal installation 1 x 4P: mounting plate support: NSX250 horizontal installation
Operating position	Horizontal

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Connection position	Connection block
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	850 mm
Net weight	1.4 kg

Quantity per set	Set of 1
Functional unit	850 mm Prisma G floor-standing enclosure human-switchboard interface 96 x 96 mm device 1 4 850 mm Prisma G floor-standing enclosure human-switchboard interface HSI 1 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed toggle horizontal 3P 1 connection block 5 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed toggle horizontal 4P 1 connection block 5 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle horizontal 3P 1 connection block 5 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle horizontal 4P 1 connection block 5 850 mm Prisma G floor-standing enclosure Enerlin'X FDM121 fixed remote control vertical 1 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed toggle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed toggle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle horizontal 4P 1 direct with long terminal shield 4

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	20.0 cm
Package 1 Length	75.0 cm
Package 1 Weight	1.4 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	16.0 cm
Package 2 Width	53.0 cm
Package 2 Length	81.0 cm
Package 2 Weight	8.76 kg
Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	97.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	99.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Halogen content performance	Halogen free plastic parts product