



### Main

Range	Vivace
Device short name	KB30
Product or component type	Fuse connection unit
Device presentation	Complete mechanism
Main colour tint	Aluminium silver
Colour tint	Aluminium silver

### Complementary

Pilot light	Neon indicator
Colour tint	Aluminium silver
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Surface Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	13 A at 250 V AC, resistive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L in L out N in N out Earth
Tightening torque	0.4 N.m
Clamping connection capacity	2 x 4 mm <sup>2</sup> input 3 x 2.5 mm <sup>2</sup> input 1 x 1.5 mm <sup>2</sup> output 1 x 2.5 mm <sup>2</sup> output
Width	87 mm
Height	87 mm






### Environment

Standards	BS 1363-4
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.5 cm
Package 1 Length	8.6 cm
Package 1 Weight	113.4 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.204 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	11594 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations