



Main

Range	PowerLogic
Device short name	DR
Product or component type	Detuned reactor
Network frequency	60 Hz
Reactive power rating	100 kvar for 400 V AC 60 Hz
Network rated voltage	400 V AC 60 Hz
Tuning order	2.7 - 162 Hz - 14 % - 60 Hz

Complementary

Power losses (max)	600 W
Value of inductance	0.676 mH
Inductance tolerance	- 5 % to 5 % per phase
Fundamental current rating	144.3 A
RMS current rating	147.2 A
Electrical insulation class	Class H
[Ui] rated insulation voltage	1.1 kV
Dielectric test voltage	4 kV 60 Hz 1 minute
[Imp] maximum permanent current	1.12 x I1
Harmonic current spectrum	5.5 % x I3 10.7 % x I5 5.3 % x I7 2.1 % x I11
Dynamic withstand current	2.2 x Isc
[Ith] conventional free air thermal current	2 A at 250 V AC 50 Hz
Type of installation	Indoor installation
Type of cooling	Forced convection
Connections - terminals	Pad terminal
Fixing center	200 x 125 mm
Height	350 mm
Width	350 mm
Depth	220 mm
Net weight	54 kg

Environment

Standards	IEC 60068
IP degree of protection	IP00
Operating altitude	<= 2000 m
Ambient air temperature for operation	0...55 °C at <= 1000 m 0...50 °C at > 1000...2000 m
Average ambient air temperature for operation	50 °C at <= 1000 m (average over 24 hours) 40 °C at <= 1000 m (average over 1 year) 45 °C at > 1000...2000 m (average over 24 hours) 35 °C at > 1000...2000 m (average over 1 year)
Climatic withstand	Relative humidity: 20...80 % Salt mist (400 V/50 Hz) : 250 hours

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	58.0 cm
Package 1 Width	40.0 cm
Package 1 Length	60.0 cm
Package 1 Weight	61.0 kg
Unit Type of Package 2	P06
Number of Units in Package 2	2
Package 2 Height	50.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	130.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations