


LVS03292

Front plate, PrismaSeT G, for VIGI NSX/CVS 250, 4M, horizontal, toggle/rotary handle, W600, white, RAL 9003



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT Pack 250 enclosure
Type of front plate	Cut-out
Installed device	ComPact: fixed NSX100...250 and ammeter without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - horizontal installation Enerlin'X: fixed FDM121 - control: remote control - vertical installation
Poles description	1 x 3P: mounting plate support: CVS100...160 horizontal installation 1 x 4P: mounting plate support: CVS100...160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation 1 x 3P: mounting plate support: NSX100...160 horizontal installation 1 x 4P: mounting plate support: NSX100...160 horizontal installation 1 x 3P: mounting plate support: NSX250 horizontal installation 1 x 4P: mounting plate support: NSX250 horizontal installation 1 x 3P: mounting plate support: NSX100...250 and ammeter horizontal installation 1 x 4P: mounting plate support: NSX100...250 and ammeter horizontal installation

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Pack enclosure - width 600 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	200 mm
Net weight	0.8 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.5 cm
Package 1 Length	51.5 cm
Package 1 Weight	802.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	16.5 cm
Package 2 Width	22.5 cm
Package 2 Length	53.0 cm
Package 2 Weight	8.304 kg
Unit Type of Package 3	P12
Number of Units in Package 3	360
Package 3 Height	102.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	310.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product