



Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Plain
Installed device	TeSys: fixed TeSys U - horizontal installation Altistart: ATS01N103/106FT Phaseo: LV/LV transformer Enerlin'X: FDM128
Poles description	9 x 3P: modular rail support: TeSys U horizontal installation

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Number of vertical modules [50 mm]	4
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	200 mm
Width	500 mm
Net weight	0.86 kg
Quantity per set	Set of 1
Functional unit	600 mm PrismaSeT G floor-standing enclosure TeSys TeSys U fixed horizontal 3P 9 direct 4 600 mm PrismaSeT G wall-mounted enclosure TeSys TeSys U fixed horizontal 3P 9 direct 4 650 mm 400 mm PrismaSeT P cubicle TeSys TeSys U fixed horizontal 3P 9 direct 4 600 mm PrismaSeT G floor-standing enclosure Altistart ATS01N103/106FT 19 4 600 mm PrismaSeT G wall-mounted enclosure Altistart ATS01N103/106FT 19 4 650 mm 400 mm PrismaSeT P cubicle Altistart ATS01N103/106FT 19 4 600 mm PrismaSeT G floor-standing enclosure Phaseo LV/LV transformer 4 600 mm PrismaSeT G wall-mounted enclosure Phaseo LV/LV transformer 4 650 mm 400 mm PrismaSeT P cubicle Phaseo LV/LV transformer 4 650 mm 400 mm PrismaSeT P cubicle Enerlin'X FDM128 4 4

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	862.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	16.5 cm
Package 2 Width	22.5 cm
Package 2 Length	52.5 cm
Package 2 Weight	8.812 kg
Unit Type of Package 3	P12
Number of Units in Package 3	360
Package 3 Height	100.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	329.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product