



## Main

Range	Linergy
Range of product	Linergy
Product or component type	Connection
Product name	Linergy FM
Product name	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P enclosure PrismaSeT Prisma iPM L enclosure PrismaSeT Prisma iPM M enclosure Linergy Linergy FM device feeder
Standards	IEC 61439-1, inside enclosure IEC 61439-2, inside enclosure
Product certifications	ASTA

## Complementary

Cubicle-device connection	Linergy FM distribution block Linergy BS rear busbar
Poles description	4P
Installation description	Enclosure - width 600 mm
[Ie] rated operational current	200 A
Colour	Anthracite grey (RAL 7016)
Net weight	0.08 kg
Quantity per set	Set of 1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	3.5 cm
Package 1 Length	8.0 cm
Package 1 Weight	75.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.25 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product