

# LVS04408

## Distribution Block, Linergy FC, for compact NSX250 4P fixed W/O Connection



### Main

Range	Linergy
Range of product	Linergy
Product or component type	Device feeder
Product name	Linergy FC
Accessory / separate part category	Connection accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle

## Complementary

Installation description	Cubicle - width 650 mm
Number of devices	3 (4P)
Poles description	4P
Installed device	<p>ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: fixed INS250 - control: direct front rotary handle - vertical installation</p> <p>ComPact: fixed INV250 - control: direct front rotary handle - vertical installation</p> <p>ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: fixed NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: fixed NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: fixed NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: fixed NSX250 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: toggle - vertical installation</p>
Mounting support	Mounting plate
Installation direction	Horizontal
[Ui] rated insulation voltage	750 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	675 A at 40 °C
[Ue] rated operational voltage	690 V
[Ipk] rated peak withstand current	50 kA
I <sup>t</sup> on activation	25000000 A <sup>2</sup> .s
Permissible current	<p>675 A at 40 °C</p> <p>615 A at 60 °C</p> <p>570 A at 70 °C</p>
Connections - terminals	Outgoer: plug in (phase / neutral) , 3 outgoing
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA[RETURN]KEMA
Quantity per set	Set of 1
Length	440 mm

Height	132 mm
Depth	235 mm
Net weight	8 kg
Colour	Black

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	24.5 cm
Package 1 Length	46.0 cm
Package 1 Weight	4.488 kg
Unit Type of Package 2	P12
Number of Units in Package 2	42
Package 2 Height	103.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	200.0 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins