



### Main

Range	Prisma
Range of product	Prisma G
Product or component type	Rail
Accessory / separate part category	Installation accessory
Range compatibility	Prisma Prisma G
Type of rail	Modular Adjustable
Installed device	ComPact: fixed NG160 without earth leakage protection ComPact: fixed NG160 with earth leakage protection ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles description	7 x 3P: fixed NG160 5 x 4P: fixed NG160 3 x 3P: fixed NG160 2 x 4P: fixed NG160 1 x 3P or 4P: fixed NSXm vertical installation

### Complementary

Installation description	Floor-standing enclosure - width 850 mm
Number of vertical modules [50 mm]	5 module(s): NG160 without earth leakage protection , direct in 850 mm Widefloor-standing enclosure 5 module(s): NSXm without earth leakage protection , direct in 850 mm Widefloor-standing enclosure 5 module(s): NG160 with earth leakage protection , direct in 850 mm Widefloor-standing enclosure 5 module(s): NSXm with earth leakage protection , direct in 850 mm Widefloor-standing enclosure
9 mm pitches	72
Quantity per set	Set of 1
Height	82 mm
Width	662 mm
Depth	169 mm
Net weight	0.4 kg
Colour	Natural
Material	Metal
Thickness	1.5 mm

### Environment

Standards	IEC 61439-2 IEC 61439-1
-----------	----------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	10.5 cm
Package 1 Length	69.4 cm
Package 1 Weight	400.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	15.5 cm
Package 2 Width	33.0 cm
Package 2 Length	73.5 cm
Package 2 Weight	4.6 kg
Unit Type of Package 3	P12
Number of Units in Package 3	140
Package 3 Height	75.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	65.24 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product